



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M3538 .5HP 1720RPM 3PH 60HZ 56 3416M Tefc F1 N

Baldor/Abb Motors & Mechanical

Catalog Number	M3538
Manufacturer	Baldor/Abb Motors & Mechanical
Description	Baldor Electric; Ac Motor; Torque Rating: 1.5 LB-FT Full Load, 7 LB-FT Break Down, 4.5 LB-FT Pull-Up, 5.3 LB-FT Locked-Roter At 460 V, 60 HZ, 0.5 HP; Temperature Rating: 40 Deg C Amambient Condition; Phase: 3 PH; Voltage Rating: 230/460 Vac; Enclosure: Tef
Weight per unit	23.0 (lbs/each)
Product Category	Motors

Features

Base	Rigid
frame	56 V
horsepower	0.5 in
Insulation Class	F
Phase	3 in
Power Factor	0.63 in
Service Factor	1.25 IN
Speed Rating	1,725 rpm
Voltage Rating	230/460 V

Descriptions

Description	.5HP 1720RPM 3PH 60HZ 56 3416M TEFC F1 N
extra long description	BALDOR M3538 .5HP,1725RPM,3PH,60HZ,
Long Description	Baldor Electric; AC Motor; Torque Rating: 1.5 LB-FT Full Load, 7 LB-FT Break Down, 4.5 LB-FT Pull-Up, 5.3 LB-FT Locked-Roter At 460 V, 60 HZ, 0.5 HP; Temperature Rating: 40 DEG C Amambient Condition; Phase: 3 PH; Voltage Rating: 230/460 VAC; Enclosure: TEF
Product Type	.5HP, 1725RPM, 3PH, 60HZ, 56, 3416M, Tefc, F1
Special Features	.5HP,1725RPM,3PH,60HZ,56,3416M,TEFC,F1

Manufacturer Information

Brand	Baldor/Abb Motors & Mechanical
GTIN	00781568101902
Manufacturers Part Number	M3538
UPC	781568101902

Taxonomies, Classifications, and Categories

Category Description	Motors
Type	AC Motors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	23

Uses, Certifications, and Standards

Application	General Purpose
Enclosure	TEFC
Frequency Rating	60 Hz
Mounting	F1