



Product Number: 64034

Order Abbreviation: M400/U/ED28

General Description: 400W METALARC compact quartz metal halide lamp, reduced outer jacket, E39 base, ED28 bulb, enclosed fixture rated, universal burn, clear, 4000K

Product Information

Abbrev. With Packaging Info.	M400UED28 6/CS 1/SKU
ANSI Code 2	M59/E
Approx. Lumens (initial - horizontal)	32000
Approx. Lumens (initial - vertical)	36
Approx. Lumens (mean - horizontal)	22
Approx. Lumens (mean - vertical)	22
Arc Length (in)	1.177
Arc Length (mm)	45
Average Rated Life - Horizontal (hr)	15000
Average Rated Life - (hr)	15000
Average Rated Life - Vertical (hr)	20000
Base	E39 Mogul
Bulb	ED28
Color Rendering Index (CRI)	65
Color Temperature/CCT (K)	4000
Diameter (in)	3.504
Diameter (mm)	89
Family Brand Name	Compact Metalarc®
Fixture Requirement	E
Hot Restrike Time (min)	7 - 12
Lamp Finish	Clear
Light Center Length - LCL (in)	5
Light Center Length - LCL (mm)	127
Maximum Base Temperature - Fahrenheit	482
Maximum Base Temperature - Celsius	250
Maximum Bulb Temperature - Fahrenheit	752
Maximum Bulb Temperature - Celsius	400
Maximum Overall Length - MOL (in)	8.31
Maximum Overall Length - MOL (mm)	211
Nominal Voltage (V)	135.00
Nominal Wattage (W)	400.00
Operating Position	Universal
Warm-up Time (min)	2 - 4



Product Number: 64034

Order Abbreviation: M400/U/ED28

General Description: 400W METALARC compact quartz metal halide lamp, reduced outer jacket, E39 base, ED28 bulb, enclosed fixture rated, universal burn, clear, 4000K

Product Information

Abbrev. With Packaging Info.	M400UED28 6/CS 1/SKU
ANSI Code 2	M59/E
Approx. Lumens (initial - horizontal)	32000
Approx. Lumens (initial - vertical)	36
Approx. Lumens (mean - horizontal)	22
Approx. Lumens (mean - vertical)	22
Arc Length (in)	1.177
Arc Length (mm)	45
Average Rated Life - Horizontal (hr)	15000
Average Rated Life - (hr)	15000
Average Rated Life - Vertical (hr)	20000
Base	E39 Mogul
Bulb	ED28
Color Rendering Index (CRI)	65
Color Temperature/CCT (K)	4000
Diameter (in)	3.504
Diameter (mm)	89
Family Brand Name	Compact Metalarc®
Fixture Requirement	E
Hot Restrike Time (min)	7 - 12
Lamp Finish	Clear
Light Center Length - LCL (in)	5
Light Center Length - LCL (mm)	127
Maximum Base Temperature - Fahrenheit	482
Maximum Base Temperature - Celsius	250
Maximum Bulb Temperature - Fahrenheit	752
Maximum Bulb Temperature - Celsius	400
Maximum Overall Length - MOL (in)	8.31
Maximum Overall Length - MOL (mm)	211
Nominal Voltage (V)	135.00
Nominal Wattage (W)	400.00
Operating Position	Universal
Warm-up Time (min)	2 - 4