

Eaton MB2040PV200BTS

Catalog Number: MB2040PV200BTS

Eaton Type BR Solar Power Center Meter Breaker, BR solar-ready, CSR main breaker, Over/under construction, 200A, 120/240V, 70 max PV input, 20 spaces, 40 circuits, 10 kAIC, Surface MTG, NEMA 3R Galv. Steel Encl., Al 225A bus, OH/UG feed

Photo is representative

General specifications

Product Name	Catalog Number
Eaton type BR solar power center meter breaker	MB2040PV200BTS
	UPC
	786685690285
Product Length/Depth	Product Height
34.7 in	6 in
Product Width	Product Weight
14.8 in	39.75 lb
Warranty	Certifications
10 year	UL Listed



defaultTaxonomyAttributeLabel

Special features

Over/under construction

Type

BR solar-ready

Utility approvals

NM : Public Service Company of New Mexico (PNM)

Enclosure material

Galvanized steel

Interrupt rating

10 kAIC

Enclosure

NEMA 3R

Input

70 max PV

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Used with

Type BR breakers

Bus Rating

225 A

Number of circuits

40

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR

Resources

Brochures

Solar power centers

Catalogs

Eaton's Volume 15—Solar Inverters and Electrical Balance of System

Specifications and datasheets

Eaton Specification Sheet - MB2040PV200BTS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)