

Eaton MB48B150BTSG

Catalog Number: MB48B150BTSG

Eaton resi meter breaker, Georgia Power, All-in-ones, 150 A, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm25 kAIC, #6-350 kcmCSR2150BM, Surface mounting, 8, Four-jaw, 1, 4, Single-phase, Ringless, GA, Georgia Power, 120/240 Vac

General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MB48B150BTSG
UPC	Product Length/Depth
786685293363	7 in
Product Height	Product Width
25.5 in	23.5 in
Product Weight	Warranty
43 lb	10 year
Certifications	
UL Listed	



Product specifications

Interrupt rating

22 kAIC

Utility approvals

GA : Georgia Power

Phase

Single-phase

Ground

#6-350 kcmil

Bus material

Aluminum

Number of jaws

Four-jaw

Main circuit breaker

CSR2150BM

Enclosure

NEMA 3R

Type

All-in-ones

Feed type

Top/bottom

Number of sockets

1

Voltage rating

120/240 V

Number of circuits

8

Resources

Brochures

[Eaton Emergency Disconnect Options at a Glance](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER BRKR DIM, DWG, MB48B200BTSG, MBPB200BTSG, RINGLESS, 200A, GA, PANEL](#)

Specifications and datasheets

[Eaton Specification Sheet - MB48B150BTSG](#)

[Technical Data Residential Meter Breakers: Type CH and BR Residential](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)