

Eaton MBE1212L200BTS

Catalog Number: MBE1212L200BTS

Eaton Meter Breaker EUSERC Type BR, Main lug, 200A, 120/240V, Ring, 12 spaces, 12 circuits, Surface mounting, Box size C, Aluminum bus, Overhead/underground feed, Four-jaws, 1 socket, #6-2/0 AWG line, #6-2/0 AWG ground



General specifications

Product Name	Catalog Number
Eaton meter breaker EUSERC	MBE1212L200BTS
UPC	Product Length/Depth
782113493749	26.8 in
Product Height	Product Width
6.3 in	17.3 in
Product Weight	Warranty
39 lb	10 year
Compliances	Certifications
EUSERC Approved	UL Listed

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

HI : Hawaiian Electric

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

WA : Puget Sound Energy

WA : Tacoma Public Utilities

Interrupt rating

10 kAIC

Box size

C

Enclosure

NEMA 3R

Ground

#6-2/0 AWG

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Used with

Type BR breakers

Number of circuits

12

Bus material

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER MBE1212L200BTS, BTF

Specifications and datasheets

Eaton Specification Sheet - MBE1212L200BTS

Technical Data Residential Meter Breakers: Type CH and BR Residential

Aluminum

Feed type

Top/bottom

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia