

Eaton MBE2040B200BTS

Catalog Number: MBE2040B200BTS

Eaton Meter Breaker EUSERC Type BR , CSR2200 main breaker, 200A, 120/240V, Ring, 20 spaces, 40 circuits, 10 kAIC, Surface mounting, Box size A, Aluminum bus, OH/UG feed, Four-jaws, 1 socket, #6-250 kcmil line, #6-250 kcmil ground

General specifications

Product Name	Catalog Number
Eaton meter breaker EUSERC	MBE2040B200BTS
UPC	Product Length/Depth
782114883594	5.5 in
Product Height	Product Width
36.06 in	16.63 in
Product Weight	Warranty
46.25 lb	10 year
Compliances	Certifications
EUSERC Approved	UL Listed



Product specifications

Interrupt rating

10 kAIC

Utility approvals

ID : Avista Utilities

WA : Avista Utilities

NM : El Paso Electric

TX : El Paso Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : City of Los Angeles - DWP (LADWP)

AZ : Southern California Edison

CA : Southern California Edison

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

AZ : Salt River Project (SRP)

HI : Hawaiian Electric

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

AZ : Tucson Electric Power/ UniSource

AZ : Sulphur Springs Valley Electric Coop

WA : Puget Sound Energy

WA : Tacoma Public Utilities

Phase

Single-phase

Ground

#6-250 kcmil

Bus material

Aluminum

Number of jaws

Four-jaw

Main circuit breaker

CSR2200

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - MBE2040B225BTS, BTF - MBE2040B200BTS, BTF

Specifications and datasheets

Technical Data Residential Meter Breakers: Type CH and BR Residential

Eaton Specification Sheet - MBE2040B200BTS

Enclosure

NEMA 3R

Type

All-in-ones

Feed type

Top/bottom

Number of sockets

1

Used with

Type BR breakers

Voltage rating

120/240 V

Number of circuits

40

Box size

A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)