

Eaton type BR solar power center meter breaker

MBE4040PV200BTS

UPC:786685690261

Dimensions:

- **Height:** 34.17 IN
- **Length:** 5.31 IN
- **Width:** 22.25 IN

Weight:45 LB

Warranties:

- 10 year

Specifications:

- **Special Features:** Side by side construction
- **Type:** BR solar-ready
- **Amperage Rating:** 200A
- **Mounting:** Surface
- **Number Of Spaces:** 40
- **Voltage Rating:** 120/240V
- **Number Of Sockets:** 1
- **Phase:** Single-phase
- **Used With:** Type BR breakers
- **Bus Rating:** 225 A
- **Input:** 70 max PV input
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Main Circuit Breaker:** CSR

Supporting documents:

- [Solar power centers](#)
- [Eaton's Volume 15-Solar Inverters and Electrical Balance of System](#)
- [Eaton Specification Sheet - MBE4040PV200BTS](#)

Certifications:



- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.