


Bridgeport Fittings Inc.

705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Fitting/KO type

Images



Application

Used to bond one continuous length of grounding conductor to an enclosure thru a 1/2" trade size knockout, inside or outside of an enclosure or panel board and provides 3-equipment bonding terminations. Meets the requirement for Intersystem Bonding. Patented

Product Information

Material: Brass-Body, Stainless Steel Screws,

Steel Locknut

Dimension A in Inches: 0.26
Dimension B in Inches: 0.325
Dimension C in Inches: 0.50
Dimension D in Inches: 0.50
Dimension E in Inches: 1.80
Dimension F in Inches: 0.62
Dimension G in Inches: 1.375

Certifications & Codes:

NEMA

Standard FB-1

:

UL File Individual components listed for use with each other; MCC-050 and IGB-050 in File

Number: E20412

UL

Standard UL467

:

UNSPS

39121613

C:

Patent

**Mumber: #D626,087 and 7,927,157

Catalog ID: MBG-050

UPC Number: 78174702374

Description: 1/2" Mighty-Bond® Intersystem Bonding

Bridge and Coupling combination

Application: Used to bond one continuous length of grounding conductor to an enclosure thru a 1/2" trade size knockout, inside or outside of an enclosure or panel board and provides 3-equipment bonding terminations. Meets the requirement for Intersystem Bonding. Patented

Trade Size: 1/2"

Std Pkg Qty: 50

Unit Qty: 10