

Eaton MBT48B125BTSBL

Catalog Number: MBT48B125BTSBL

Eaton resi meter breaker, Barrel Lock provision, All-in-ones, 125A, C, Aluminum, NEMA 3R, Bottom and top, #6-300 kcm22 kAIC, #6-300 kcmCSR2150, Surface mounting, 8, Four-jaw, 1, 4, Single-phase, Ringless, TN, 120/240 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton residential meter breaker	MBT48B125BTSBL
UPC	Product Length/Depth
786685970929	4.94 in
Product Height	Product Width
25.5 in	14.44 in
Product Weight	Warranty
36.5 lb	10 year
Certifications	
UL Listed	

Type

All-in-ones

Utility approvals

IN : Indiana Michigan Power (IMP) (AEP East)

MI : Indiana Michigan Power (IMP) (AEP East)

OH : AEP Ohio (AEP East)

TN : Appalachian Power (AEP East)

VA : Appalachian Power (AEP East)

WV : Appalachian Power (AEP East)

IL : Ameren

MO : Ameren

Interrupt rating

22 kAIC

Enclosure

NEMA 3R

Amperage Rating

125 A

Phase

Single-phase

Bus material

Aluminum

Feed type

Top/bottom

Specifications and datasheets

[Eaton Specification Sheet - MBT48B125BTSBL](#)