

Eaton MBX2040B200BTS

Catalog Number: MBX2040B200BTS

Eaton resi meter breaker, All-in-ones, 200A, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm22 kAIC, #6-350 kcmCSR, Surface mounting, 40, Four-jaw, 1, 20, Single-phase, Ringless, Used with BR breakers, 120/240 Vac, Lever bypass



General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MBX2040B200BTS
UPC	Product Length/Depth
786685384474	5 in
Product Height	Product Width
32 in	12 in
Product Weight	Warranty
40 lb	10 year
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

IL : Ameren

MO : Ameren

CO : Xcel Energy

MI : Xcel Energy

MN : Xcel Energy

ND : Xcel Energy

NM : Xcel Energy

SD : Xcel Energy

TX : Xcel Energy

WI : Xcel Energy

CT : Eversource (Connecticut Light and Power Co./Nstar/PSC
New Hampshire/Western Mass Electric)

MA : Eversource (Connecticut Light and Power Co./Nstar/PSC
New Hampshire/Western Mass Electric)

NH : Eversource (Connecticut Light and Power Co./Nstar/PSC
New Hampshire/Western Mass Electric)

Interrupt rating

10 kAIC

Enclosure

NEMA 3R

Ground

#6-350 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Bypass

Lever

Number of circuits

40

Bus material

Aluminum

Feed type

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - C-H SKT/BKR COMBO 200A

Specifications and datasheets

Eaton Specification Sheet - MBX2040B200BTS

Top/bottom

Main circuit breaker

CSR

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)