



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MC150T7.5UG12830 MH Lamp

Sylvania-Ledvance

Catalog Number	MC150T7.5UG12830
Manufacturer	Sylvania-Ledvance
Description	OBS64968 Metalarc Powerball 150W Ceramic Metal Halide Tubular T6, Clear, Universal Operation, G12 Base, 3000K CCT, 91 Cri, Pulse Start, Enclosed Rated, 20, 000 Hour Rated Life
Weight per unit	0.1100 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	G12
lumens	15100
Shape	T7.5
Voltage Rating	93
Wattage	150

Material, Color, and Finish

color rendering index (cri)	89
color temperature	3000

Descriptions

Description	MH LAMP
extra long description	SYL MC150T6/U/G12/930/64968 WRT MC1
Long Description	OBS64968 METALARC POWERBALL 150W ceramic metal halide tubular T6, clear, universal operation, G12 base, 3000K CCT, 91 CRI, pulse start, enclosed rated, 20,000 hour rated life
Product Type	WRT MC150T6UG12930 12/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135649684
Manufacturers Part Number	MC150T6/U/G12/930/64968
sub brand	POWERBALL CERAMIC METALARC TUBULAR SINGLE-ENDED
UPC	046135649684

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
Type	High Intensity Discharge (HID)

Packaging

Carton	1
Package	12
Weight Per each	0.11



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

C142/E