## IoPhic<sup>®</sup> Smoke & Fire, Carbon Monoxide & Natural Gas Alarm 120 Volt AC Hardwired with Battery Backup

# Model MDSCN111





Protects Against Responds Responds Quickest to 87% Faster\* to Slow Fast Flaming Smoldering Fires Fires & **Natural** Carbon Monoxide Gas \* Compared to maximum allowable alarm time. UL217 Smoldering Test Profile Figure 45.3

ΤМ

NEW 4-in-1 Smart Alarm uses a single sensor to detect both CO & Natural Gas AND protects against both fast flaming & slow smoldering fires. Microprocessor Intelligence provides superior nuisance alarm resistance, along with temperature & humidity compensation, self diagnostics and Quick Find® alarm origination features. Perfect for new or replacement installations. This 120 Volt AC/DC hardwired alarm offers time-saving installation features, value & quality.

Features	Benefits					
loPhic Universal Sensing Technology $^{ extsf{R}}$	Responds 87% Faster* to slow smoldering fires AND responds quickest to fast flaming fires					
Patent pending microprocessor	Virtually eliminates nuisance alarms caused by non-hazardous sources such as cooking smoke					
Auto sensitivity calibration	Prevents nuisance alarms and provides consistency					
Self-diagnostics feature	Performs a status check upon power up to ensure alarm is functioning properly					
Ambient condition compensation	Automatically adjusts sensitivity for changes in temperature & humidity, reducing nuisance alarms					
Quick Find® alarm origination feature	Patented feature easily identifies first alarm to sound in interconnected system					
Quick activation pull tab	Preserve battery life. Preinstalled battery is quickly activated without removing alarm from bracket					
Universal mounting bracket	Fits any standard wiring junction box, single gang, round or octagon, up to 4"					
Larger mounting base	Covers drywall imperfections and old paint marks					
Product end-of-service life warning	Sounds when it is time to replace the alarm in approximately 7 years from the date of activation					
Front-load battery drawer	Replace battery without removing alarm from bracket					
Interconnectable	Up to 24 USI or Universal brand devices using existing wiring and mounting (battery drawer models)					
2 tamper resistant locking features	Prevents unauthorized alarm and battery removal					
9 Volt battery backup	Provides continuous protection in the event of power outage					

### **Technical Specifications**

Sensor Type:	IoPhic <sup>®</sup> Universal Sensing Technology
Primary Power:	120 Volt AC 60 Hz
Battery Backup:	9 Volt Energizer alkaline battery (included)
Audible Alarm:	85 dB at 10 feet
Temperature Range:	32º F to 100º F (0º C to 38º C)
Humidity Range:	10% to 95% RH
Interconnect:	Maximum 24 USI/Universal devices
LED:	4 LED's: alarm, power, CO, gas
Size:	5.63″ x 5.63″ x 1.75″
Warranty:	7 year limited

### **Regulatory Compliance:**

California State Fire Marshal (CSFM) National Fire Protection Association (NFPA) Housing and Urban Development (HUD) Federal Housing Authority (FHA) Conforms to UL Std. UTGT / UTHA / CZHF (UL)



	Box or	SHELF PACK (in.)	WEIGHT			MASTER CTN (in.)	WEIGHT	
MODEL BRAND	Clam QT	/ LxWxH	(Lbs.)	UPC CODE	QTY	L x W x H	(Lbs.)	I2 of 5
MDSCN111 USI	Box 1	5.75 x 8.75 x 1.75	0.65	0-42741-00111-3	4	7.25 x 6.25 x 8.00	2.87	1-00-42741-00111-0

A E B SECURITY INSTRUMENTS, INC. ALWAYS WORKING TO PROTECT YOUR FAMILY

#### **Corporate Office**

11407 Cronhill Dr., Suite A, Owings Mills, MD 21117 Phone: 800.390.4321 Fax: 410.363.2218 Web: www.UniversalSecurity.com www.UsiElectric.com

© 2010 Universal Security Instruments, Inc. Rev. 72812 CM116



UL 217 UL 2034 UL 1484