



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353



MHF2246PCS 2-2-4-6 Mobile Home Feeder Alu PCS

King Wire Inc.

Catalog Number	MHF2246PCS
Manufacturer	King Wire Inc.
Description	Mobile Home Feeder Cable, Flame Retardant;Moisture Resistant;Sunlight Resistant Additional Information, Mobile Home Application, Aluminum Alloy Conductor Material, 2-2-4-6 Awg Conductor Size, 100 A Current Rating, Polyethylene (XLpe) Insulation Material, 60 Mil Insulation Thickness, Made In Usa, +90 °C Maximum Operating Temperature, 0.884 In Outside Diameter, Reel Package Type, Strand Solid/Strand, Directive 2002/95/Ec;Federal Specification A-A-59544;Nec Nfpa 70, 2011 Edition;Rohs Compliant;UI 44;UI 84 Sta
Weight per unit	0.3460 (lbs/ft)
Product Category	Direct Burial Wire

Descriptions

Description	2-2-4-6 MOBILE HOME FEEDER ALU PCS
-------------	------------------------------------

Manufacturer Information

Brand	Aluminum
-------	----------

Taxonomies, Classifications, and Categories

Category Description	Direct Burial Wire
----------------------	--------------------

Packaging

Carton	1
Weight Per foot	0.346