




CATALOG NUMBER	DESCRIPTION
HIGH-BAYS	
ALUMINUM UNIT PACKS	
	HIGH PRESSURE SODIUM
	HPSS40 400W HPS Multi-Tap 15" w/Lamp
	METAL HALIDE
	MHSS40 400W MH Multi-Tap 15" w/Lamp
	MHSS40-5T 400W MH 5-Tap 15" w/Lamp
	MHSS40-5T-OR 400W MH 5-Tap 15" w/Open Rated Socket Lamp
	MHSS40-OR 400W MH Multi-Tap 15" w/Open Rated Socket Lamp
	MHSS40Q-5T 400W MH 5-Tap 15" w/Lamp & Quartz Unit Pack
	MHSS40Q-5T-OR 400W MH 5-Tap 15" w/Open Rated Socket Lamp & Quartz
	PULSE START METAL HALIDE
MPSS40 400W MP Multi-Tap 15" w/Lamp	
MPSS40-OR 400W MP Multi-Tap 15" Open Rated Socket w/Lamp	
ACRYLIC UNIT PACKS	
MHSS40-PD-5T 400W MH 5-Tap 22" w/Lamp	
MHSS40-PD-5T-OR 400W MH 5-Tap 22" w/Open Rated Socket Lamp	
STEELER BALLAST HOUSINGS	
	HIGH PRESSURE SODIUM
	HPSS-250-MT 250W HPS Multi-Tap
	HPSS-400-MT 400W HPS Multi-Tap
	HPSS-400-480V 400W HPS 480V
	HPSS-1000-MT 1000W HPS Multi-Tap
	HPSS-1000-480V 1000W HPS 480V
	METAL HALIDE
	MHSS-250-MT 250W MH Multi-Tap
	MHSS-400-MT 400W MH Multi-Tap
	MHSS-400-MT-L/TCB 400W MH Multi-Tap/Less TCB (Use TWMBSS Accessory)
MHSS-400-MT-Q 400W MH Multi-Tap & Quartz	
MHSS-400-5T 400W MH 5-Tap	
MHSS-400-480V-Q 400W MH 480V & Quartz	
MHSS-400-5T-OR 400W MH 5-Tap w/Open Rated Socket	
MHSS-400-MT-OR-Q 400W MH Multi-Tap w/Open Rated Socket & Quartz	
MHSS-1000-MT 1000W MH Multi-Tap	
MHSS-1000-480V 1000W MH 480V	
MHSS-1000-MT-Q 1000W MH Multi-Tap & Quartz	
MHSS-1000-MT-OR 1000W MH Multi-Tap w/Open Rated Socket	
MHSS-1000-MT-OR-Q 1000W MH Multi-Tap w/Open Rated Socket & Quartz	
MHSS-1000-480V-OR 1000W MH 480V w/Open Rated Socket	
PULSE START METAL HALIDE	
MPSS-320-MT-OR 320W MP Multi-Tap w/Open Rated Socket	
MPSS-320-MT-OR-Q 320W MP Multi-Tap w/Open Rated Socket & Quartz	
MPSS-350-MT-OR 350W MP Multi-Tap w/Open Rated Socket	
MPSS-350-MT-OR-Q 350W MP Multi-Tap w/Open Rated Socket & Quartz	
MPSS-400-MT 400W MP Multi-Tap	
MPSS-400-MT-Q 400W MP Multi-Tap & Quartz	
MPSS-400-MT-OR 400W MP Multi-Tap w/Open Rated Socket	
MPSS-400-MT-OR-Q 400W MP Multi-Tap w/Open Rated Socket & Quartz	
BENCHMARK BALLAST HOUSINGS	
	METAL HALIDE
	MHBB-250-MT 250W MH Multi-Tap
	MHBB-400-MT 400W MH Multi-Tap
	ECON™ ELECTRONIC PULSE START METAL HALIDE
	MDHB-320-E-OR 320W ECON™ MP 208-277V w/Open Rated Socket
	MDHB-400-E-OR 400W ECON™ MP 208-277V w/Open Rated Socket
	REFLECTORS/ENCLOSURES/WIRE GUARDS [OPEN HIGH-BAYS]
	ALUMINUM REFLECTORS
	SA15 15" Aluminum High-Bay Reflector
	SA15E 15" Aluminum High-Bay Reflector w/Quartz Mounting
	SA18 18" Aluminum High-Bay Reflector
	SA18E 18" Aluminum High-Bay Reflector w/Quartz Mounting
	SA23 23" Aluminum High-Bay Reflector
	SA23E 23" Aluminum High-Bay Reflector w/Quartz Mounting
	AV19 19" VertX Aisle Lighter
	ENCLOSURES
	SGB15 15" Safety Glass Bottom
	SGB18 18" Safety Glass Bottom
	SGB19 19" VertX Safety Glass Bottom
	SGB23 23" Safety Glass Bottom
	REFLECTORS/ENCLOSURES/WIRE GUARDS [OPEN HIGH-BAYS]
	WIRE GUARDS
	WG15 15" Wire Guard
	WG15/GLC 15" Wire Guard w/Safety Glass
	WG18 18" Wire Guard
	WG18/GLC 18" Wire Guard w/Safety Glass
	WG23 23" Wire Guard