# $\mathsf{MINILITER}^*\,\mathsf{V}$ **SERIES**



**Approvals** 

#### **SPECIFICATIONS**

#### **Intended Use:**

Sign, facade, area, accent and general security lighting

### **Construction:**

· Die-cast aluminum housing and door, rugged, corrosion resistant and compact

Cat.#

Job

- Tempered, impact resistant glass lens
- Tool-free entry for easy maintenance twin stainless steel eccentric latches
- Protective dark bronze powder paint finish
- Effective Projected Area (EPA) is 1.4 sq. ft.

#### **New UST Verstions:**

UST fixtures are built in Christiansburg, VA and are offered with an array of options including finish color, cord, fusing, twist lock photocell receptacle and quartz standby; Units meet ARRA level 2

### Optics:

- Silicone lens/door gasket provides positive seal
- Wide, uniform beam with high efficiency for maximum beam coverage, spread covers are four times the set-back

### Electrical:

HPF ballastry in Quad-Tap® (120,208,240,277V), or 480V

#### Installation:

Steel yoke (MHS-Y) with three-hole pattern allows versatile mounting. Cast aluminum knuckle (MHS-K) slip-fits 23/8" OD tenons/pipe, provides concealed wiring for appearance and safety.

Type

## Listings:

LIsted to UL 1598 for use in wet locations, CSA 22.2 No. 250.0-00, suitable for wet locations. U.S. Patent No. 6,461,026


# Warranty:

For more information visit: http://www.hubbelloutdoor.com/resources/warranty/

# **CERTIFICATIONS/LISTINGS**



# PRODUCT IMAGE(S) MHS YOKE MOUNT



A	В	C	D	E	F	G	Н	- 1
6 1/2"	14 1/2"	12"	9 7/8"	16 1/4"	3 1/8"	17/32"	7/8"	17"
165 mm	368 mm	305 mm	251 mm	413 mm	79 mm	14 mm	22 mm	432 mm

voltage: 1-120V, 2-208V, 3-240V, 4-277V, 5-480V,

6-347V)


# **ORDERING INFORMATION** - Stock

Catalog Number	Lamp Type/Wattage <sup>1</sup>	Voltage	Weight lbs. (kg)			
Pulse Start Metal Halide Yoke Mount						
MHS-Y250P8	250W PS ED28	Quad-Tap® (120, 208, 240, 277V)	22 (10.0)			
MHS-Y150P8	150W MH ED28	Quad-Tap <sup>®</sup> (120, 208, 240, 277V)	21 (9.5)			
Pulse Start Metal Halide Knuckle Mount						
MHS-K400P8	400W PS ED37	Quad-Tap® (120, 208, 240, 277V)	31 (14.1)			
MHS-K250P8	250W PS ED28	Quad-Tap <sup>®</sup> (120, 208, 240, 277V)	27 (12.2)			

All fixtures have dark bronze powder finish and are shipped with mogul base lamp NOTE: EPA is 1.4 sq. ft.

### **ORDERING INFORMATION** – UST

ORDERING EXAMPLE: MHS-Y-400P-8-BZ-C3




Note: Lamps not included

# **ACCESSORIES** - Order Separately


Ostala v Nevakav	Description
Catalog Number	Description
PBT-1	Photocontrol, button type, 120V
PBT-234	Photocontrol, button type, 208, 240, 277V
MHS4-SPC	Polycarbonate shield (for independent use only)
MHS4-G	Wire guard, 2" square grid (for independent use only)
4024C	Steel slipfitter for 2" pipe, 2 3/8" OD yoke mount, bronze finish
MHS4-GS	Glare shield, black finish (for independent use only)
MHS4-VGS	Vertical glare shield, black finish (for independent use only)
MHS4-HGS	Horizontal glare shield, black finish (for independent use only)
MHS-21	Two light bracket, bolt on yoke mount, slipfits 2 3/8" OD tenons, bronze finish
SSB-21-M51	Two light bracket, knuckle mount units, slipfits 2 3/8" OD tenons, bronze finish
TWK-11	Steel wall bracket with 2 3/8" tenon, bronze finish (use with MHS-K)

# REPLACEMENT PARTS

Catalog Number	Description	
93011267	Replacement lens door	



# **PHOTOMETRICS** For additional photometric information and IES downloads, visit our web site at www.hubbelloutdoor.com



# PHOTOMETRIC REPORTS

Catalog Number	Report #
MHS-X175H-46X-X (MHS-X150P)	HP08366.IES
MHS-X250H-46X-X	HP08362.IES
MHS-X400H-46X-X	HP08348.IES
MHS-X400S-46X-X	HP08349.IES

