

1-Gang Weatherproof In-Use Cover, Expandable, EXTRA DUTY®, White

By TayMac Catalog # ML500W

1-Gang Weatherproof In-Use Cover, Expandable, EXTRA DUTY*, White



Features

- Revolutionary design expands from 1 in. to 3 in. for In-Use needs
- Ultra-rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 16-in-1 custom device configurations, comes pre-configured for GFCI
- 100% paintable surface
- Clear window allows for quick/easy visual inspection
- · Includes attached gasket and mounting hardware
- NEMA 3R compliant

General

Color White
Construction Nonmetallic
Cover Type Expandable;In-Use
Material Polycarbonate
Mounting Method Multi-directional

Number of Gang(s) 1-Gang Type Cover

UPC 050169917428

Weather Resistant Yes

Dimensions

Cubic Capacity 74.4168 cu.in

 Depth
 3 in

 Height
 6.14 in

 Weight
 0.445 lb

 Width
 4.04 in

Certifications and Compliance

Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Packaging Type	Shrink
Pallet Quantity	1890
Standard Package	10

Product Assets

Brochures - BL BRO OC-218

Brochures - TayMac Extra Duty In-use Covers Catalogs - RACO / TayMac / Bell Full Catalog

Customer Notices - Prop 65 - Cancer & Reproductive Harm

Notice

Product Logo - ExtraDuty

Product Logo - OutdoorComforts

Sales Drawings - ML500

SDS - HCC_SDS

Terms and Conditions - HCC Terms & Conditions Video - TAYMAC: ML Series Expandable In-Use Covers

Video - TAYMAC: Extra-Duty Overview