



1-Gang Weatherproof In-Use Cover, Expandable, EXTRA DUTY®, Bronze

By TayMac
Catalog # [ML500Z](#)

1-Gang Weatherproof In-Use Cover, Expandable, EXTRA DUTY®, Bronze



Features

- Revolutionary patented design expands from 1 in. to 3 in. for In-Use needs
- Ultra-rugged polycarbonate & synthetic neoprene rubber that will not dry-rot, crack or deteriorate in sunlight
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 16-in-1 custom device configurations, comes pre-configured for GFCI
- 100% paintable surface
- Clear window allows for quick and easy visual inspection
- Includes attached gasket and mounting hardware
- NEMA 3R compliant

General

Color	Bronze
Construction	Nonmetallic
Cover Type	Expandable;In-Use
Material	Polycarbonate
Mounting Method	Multi-directional
Number of Gang(s)	1-Gang
Type	Cover
UPC	050169917435
Weather Resistant	Yes

Dimensions

Cubic Capacity	74.4168 cu.in
Depth	3 in
Height	6.14 in
Weight	0.474 lb
Width	4.04 in

Certifications and Compliance

Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	10
Packaging Type	Shrink
Pallet Quantity	1890
Standard Package	10

Product Assets

[Brochures - TayMac Extra Duty In-use Covers](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Product Logo - ExtraDuty](#)
[Product Logo - OutdoorComforts](#)
[Sales Drawings - ML500](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TAYMAC: ML Series Expandable In-Use Covers](#)
[Video - TAYMAC: Extra-Duty Overview](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
TAYM-ML500Z-SPEC-EN | REV 8/2023