



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MLT2SCP316 SS Tie Bulk-PK

Panduit Corporation

Catalog Number	MLT2SCP316
Manufacturer	Panduit Corporation
Description	The MLT2S-CP316 Self-Locking Cable Tie Speeds Up Installation With A Unique Self-Locking Head Design That Locks Into Place At Any Part Along The Tie Body. The Smooth Surfaces and Rounded Edges Assure Cable Protection and Worker Safety. Provides A Strong, Durable Method Of Cabling Bundle and Can Be Used In A Wide Range Of Indoor, Outdoor, and Underground Applications.
Weight per unit	0.0010 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	200

### Dimensions and Weight

Length	7.9
--------	-----

### Descriptions

Description	SS TIE BULK-PK
extra long description	PAN MLT2S-CP316 Pan-Steel® MLT2S-CP
Long Description	The MLT2S-CP316 self-locking cable tie speeds up installation with a unique self-locking head design that locks into place at any part along the tie body. The smooth surfaces and rounded edges assure cable protection and worker safety. Provides a strong, durable method of cabling bundle and can be used in a wide range of indoor, outdoor, and underground applications.
Product Type	Pan-Steel® MLT2S-CP316 Cable Tie, SS 316, Standard, 2" Dia.,
Special Features	Harsh

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983543991
Manufacturers Part Number	MLT2S-CP316
UPC	074983543991

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	2000
Package	100
Weight Per each	0.001

## Uses, Certifications, and Standards

Application	Harsh Environment
standard	UL E56854,CE,ABS,GL,SAE,BV,LR,DNV