

RACO' TAYMAC' BELL

SINGLE AND TWO GANG FLAT COVERS

Two Gang Flat Covers 2-Gang 55-in-1

C06





Catalog #: MM1410C

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use.

PRODUCT FEATURES

High-impact polycarbonate construction provides maximum durability Patented Quick-Fit™ keyhole mounting system allows installation in under a minute. Includes attached gasket and mounting hardware Pre-configured for GFCI with patented Knockout technology for alternate devices Lockable tab

UL LISTED

File E116141

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

GENERAL PRODUCT INFORMATION

Color: Clear Country of Origin: USA

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Depth: 5/8 in. Wt. Ea. (Lbs.): 0.546

PACKAGING

Package Type: Shrink

Std. Pkg.: 10

Product UPC-A Labeled: Yes

Weight (Lbs. Per/C): 54.60

Ship Carton Length (in.): 20.88

Ship Carton Width (in.): 5.13

Ship Carton Height (in.): 6.63

Ctn Weight (Lbs.): 5.46

Pallet Qty: 1260.00

UPC Number: 092326100625

Izof5: 40092326100623