

Search Catalog

By Keyword

All Categories VJ Series Enclosure with Stainless Steel Padlockable Latch(s) and a Stainless Steel Piano Hinge

Shopping Cart [0 items](#)
Request for Quote [0 items](#)

[All Categories](#) > [APO Series Enclosures](#)
[7" X 6" to 24" X 24"](#) > [VJ Series Enclosure with Stainless Steel Padlockable Latch\(s\) and a Stainless Steel Piano Hinge](#) > Item # VJ1008HWPL1

Item # VJ1008HWPL1 VJ Series Enclosure with Stainless Steel Padlockable Latch(s) and a Stainless Steel Piano Hinge
\$107.1153

-
-
-

VJ Series Enclosure with Stainless Steel Padlockable Latch(s) and a Stainless Steel Piano Hinge

- All VJ Series enclosures are designed to meet the Joint Industrial Council (JIC) standards in the United States.
- VJ's are made from corrosion resistant hot compression molded fiberglass reinforced polyester and do not contain halogens.
- The VJ series "HWPL" enclosures include one or two stainless steel padlockable latches to secure one side of the cover to the base and a stainless steel piano hinge that secures the other. Rivets connect the hinge to the cover and self-tapping screws connect the screws to the base.
- Seven sizes are available from 6 x 6 inch to 18 x 16 inch
- Vynckier's VJ enclosures are capable of withstanding continuous temperatures from -58°F (-50°C) up to 302°F (150°C).
- VJ enclosures provide protection for equipment and operators from indirect electrical contact.
- All VJ enclosures are UL listed per UL Standard 508 for NEMA 3, 3R, 4, 4X, 12 and 13; CSA Certified per Standard C22.2-0, 0.4, 0.7, 0.6, 94 Type 3, 3R, 4, 4X, 12 and 13.



[larger image](#)



[larger image](#)

Specifications	VJ Series Features	VJ Polyester Cover Enclosures - Optional Accessories
FRP UL Type Rating	3, 3R, 4, 4X, 12, 13	
Temperature Resistance (°F)	-58 to +302	
Temperature Resistance (°C)	-50 to +150	
Outside Height (inch)	1.31	
Outside Height (mm)	287.4	
Outside Width (inch)	9.31	
Outside Width (mm)	236.6	

Outside Depth (inch)	5.43
Outside Depth (mm)	138.0
Inside Dim. A (inch)	10.00
Inside Dim. A (mm)	254.0
Inside Dim. B (inch)	8.00
Inside Dim. B (mm)	203.2
Inside Dim. C (inch)	4.69
Inside Dim. C (mm)	119.0
Weight (lbs)	4.8
Weight (kg)	2.17
Mounting Plate Part No. (Aluminum Steel Non-Metallic)	MP1008A MP1008N MP1008S
Dim. Mounting Plate (inch)	8.75 x 6.88
Dim. Mounting Plate (mm)	222 x 175
Front Panel - Plain	VFP1008A
Front Panel - Hinged	VFPH1008A
Dim. E (inch)	1.62
Dim. E (mm)	41.2
Dim. F (inch)	4.01
Dim. F (mm)	101.8
Dim. I (inch)	0.37
Dim. I (mm)	9.5
Dim. J (inch)	10.75
Dim. J (mm)	273.0
Dim. K (inch)	6.00
Dim. K (mm)	152.5
Dim. L (inch)	0.31
Dim. L (mm)	8.0
Dim. M (inch)	0.12
Dim. M (mm)	3.0
Dim. N (inch)	11.50
Dim. N (mm)	292.0
Dim. O (inch)	6.24
Dim. O (mm)	158.5
Dim. P (inch)	8.25
Dim. P (mm)	209.5
Dim. Q (inch)	0.08
Dim. Q (mm)	2.0
Dim. R (inch)	5.14
Dim. R (mm)	130.5
Latch Spacing (inch)	Ctr
Latch Spacing (mm)	Ctr
UPC Code	635394012614
Availability	Stock
Shipment in Days	1