



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996



MPR1000VBUH00 1000W or MH Mog Base Base Up Burn Pos Lamp

Ge By Current Lamps

Catalog Number	MPR1000VBUH00
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 3500 K, 107000 LM Brightness (Lumens), 1000 W, Clear, Hard Glass Material, 12000 H Average Life, Mogul Base, M47 Ansi Ballast Code, Non Dimmable, 7 In Diameter, 15.37 In Height, 144.9 % Mercury Content, 10.35 LB
Weight per unit	1.7 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (EX39)
lumens	110000

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	1000W OR MH MOG BASE BASE UP BURN POS LAMP
extra long description	GEL MPR1000/VBU/HO/O 41433 MULTIVAP
Special Features	15.37IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168414333
UPC	043168414333

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	1.73