

# Eaton MST01

Catalog Number: MST01

Eaton NEMA starter, Space SVG reversing starter, Ground fault, 1NO contacts, 208V Coil, Nema Size 0, 0.35-1.65 A

## General specifications



Product Name	Catalog Number
Eaton NEMA starter	MST01
UPC	Product Length/Depth
786678201238	5.5 in
Product Height	Product Width
6.3 in	1.77 in
Product Weight	Warranty
1.12 lb	1 year
Certifications	Catalog Notes
UL Listed CSA Certified	Does not include heater.

## defaultTaxonomyAttributeLabel

### Horsepower

0.25 hp, 1 hp

### Number Of Poles

Single-pole

### Type

Open

### Voltage rating

120/240 Vac, 277 Vac at 1 hp, 120/240 Vac, 32 Vdc at 0.25 hp

### Size

NEMA size 0

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - MST01](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)