



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1135 Butler Road
77573-0000, TX League City
Phone: 281-833-5333
Fax: 281-833-5334



MVR400UED28 400W ED28 Metal Halide Reduced Glass Clear Mogul

Ge By Current Lamps

Catalog Number	MVR400UED28
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 33100 LM (Horizontal);36000 LM (Vertical) Brightness (Lumens), 400 W, Clear, Hard Glass Material, 15000 H (Horizontal);20000 H (Vertical) Average Life, Mogul Base, M59 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 61.11 % Mercury Content, 5.92 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
Wattage	400

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Style	Enclosed fixtures only

Descriptions

Description	400W ED28 METAL HALIDE REDUCED GLASS CLEAR MOGUL
extra long description	GEL MVR400/U/ED28 18904 MULTIVAPOR
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168189040
UPC	043168189040

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------