



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St  
70123-0000, LA Harahan  
Phone: 504-264-9995  
Fax: 504-264-5996



## MVR400UPA 400W P/S Metal Halide Universal Burn Lamp

*Ge By Current Lamps*

Catalog Number	MVR400UPA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 60, 4000 K, 31200 LM (Horizontal);39400 LM (Vertical) Brightness (Lumens), 400 W, Clear, Hard Glass Material, 15000 H (Horizontal);20000 H (Vertical) Average Life, E39 Mogul Screw Base, M135/M155 Ansi Ballast Code, Non Dimmable, 4.62 In Diameter, 11.5 In Height, 61.11 % Mercury Content, 4.45 LB
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
Wattage	400

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	60
Finish	Clear
Style	Enclosed fixtures only

### Descriptions

Description	400W P/S METAL HALIDE UNIVERSAL BURN LAMP
extra long description	GEL MVR400/U/PA 78666 MULTIVAPOR
Special Features	11.5IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168786669
Manufacturers Part Number	MVR400/U/PA
UPC	043168786669

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.74

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------