



2-Gang Weatherproof In-Use Cover, EXTRA DUTY®, Expandable, Vertical, 55-in-1, 3-1/2 in. Deep, Gray

By TayMac
Catalog # [MX7280S](#)

2-Gang Weatherproof In-Use Cover, EXTRA DUTY®, Expandable, Vertical, 55-in-1, 3-1/2 in. Deep, Gray



Features

- Revolutionary patented design expands from 2 in. to 3-1/2 in. for in-use needs
- Heavy duty die-cast metal construction with premium powder coat
- Quick-Fit keyhole mounting system allows installation in under a minute
- Universal Fit Adapter System Technology (U-Fast) for 55-in-1 custom device configurations, comes pre-configured for GFCI
- Lockable open or closed and fits fullsize padlock
- Extra Duty® rated
- Vertical mount

Application

Designed for use whenever weatherproof protection is required while an outlet is in use.

General

Color	Gray
Construction	Metallic
Cover Type	In-Use;Low Profile
Material	Aluminum
Mounting Method	Vertical
Number of Gang(s)	2-Gang
Type	Cover
UPC	092326101370

Dimensions

Actual Depth	2.282 in
Cubic Capacity	122.58519 cu.in
Depth	3.5 in
Height	6.492 in
Weight	1.069 lb
Width	5.395 in

Certifications And Compliance

Certified Listed	UL Listed
Nema Rating	NEMA 3R

Logistics

Carton Quantity	2
Packaging Type	Shrink
Pallet Quantity	624
Standard Package	2

Product Assets

[Brochures - TayMac Extra Duty In-use Covers](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - In-Use Covers and Conduit Bodies C1-C40_1](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Product Logo - ExtraDuty](#)
[Sales Drawings - MX7280S](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - TAYMAC: Metallic Extra Duty Weatherproof In-Use Device Covers](#)
[Video - TAYMAC: Extra-Duty Overview](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
TAYM-MX7280S-SPEC-EN | REV 5/2024