



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy  
75234-0000, TX Farmers Branch  
Phone: 972-206-0016  
Fax: 972-352-2818



## MXR100UMEDO 100W or PS/MH Med Screw Universal Burn Position

*Ge By Current Lamps*

Catalog Number	MXR100UMEDO
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 70, 3200 K, 9000 LM Brightness (Lumens), 100 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M90 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.4375 In Height, 9.8 % Mercury Content, 1.78 LB
Weight per unit	0.3000 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Medium Screw (E26)
lumens	9000
Wattage	100

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	70
Finish	Clear
Style	Open or enclosed fixtures

### Descriptions

Description	100W OR PS/MH MED SCREW UNIVERSAL BURN POSITION
extra long description	GEL MXR100/U/MED/O 12381 MULTIVAPOR
Special Features	5.43IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168123815
UPC	043168123815

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.3

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------