



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## N10SP 1/0 Al-Cu Split Bolt

*Nsi Industries*

Catalog Number	N10SP
Manufacturer	Nsi Industries
Description	
Weight per unit	0.1900 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	TIN PLATED COPPER
Number of Conductors	2 IN
Poles	1 IN
Voltage Rating	600 VAC
Wire Size	6 SOL - 1/0 STR
Wire Type	Class A & B

### Material, Color, and Finish

Color	SILVER
Finish	Tin Plated Copper

### Dimensions and Weight

Size	L=1.417 - W=.787 IN
------	---------------------

### Descriptions

Description	1/0 AL-CU SPLIT BOLT
Product Type	Copper Split Bolt 1/0 Tin Plated
Special Features	6 SOL-1/0 STR - 20 Pack

### Manufacturer Information

Brand	NSi
GTIN	00662381020369
Manufacturers Part Number	N-1/OSP
sub brand	Split Bolts
UPC	662381020369

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Tin Plated Copper Split Bolt

### Packaging

Carton	1
Package	20
Weight Per each	0.19



# ELLIOTT ELECTRIC SUPPLY


We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 WTT
standard	UL486B
Temperature Rating	90 WTT

## All Purpose Type Split Bolts - N-1/0SP

<b>Drawn - SD</b>	
<b>Approved - KM</b>	
<b>Material - Copper / Finish: Tin Plated</b>	
<b>Title - All Purpose Type Split Bolts</b>	
	
<b>Max Run To Max Tap</b>	<b>1/0 - 1/0 Str AL CU</b>
<b>Min Run To Min Tap</b>	<b>2 - 10 Str AL CU</b>
<b>Max Run To Min Tap</b>	<b>1/0 - 10 Str AL CU</b>
<b>Min Equal Run - Tap</b>	<b>4 - 4 Str AL CU</b>
<b>4</b>	<b>Spacer Electrolytical Copper</b>
<b>3</b>	<b>Nut Bronze</b>
<b>2</b>	<b>Rider Bronze</b>
<b>1</b>	<b>Body Electrolytical Copper</b>

