

# Eaton N224SS6

Catalog Number: N224SS6

Eaton B-Line series spring nut, 0.85"Hx1.75"Lx1.31"W, Stainless steel type 316, 1/4"-20 bolt size, 250 lbs load rating, 300 lbs load rating



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series spring nut	N224SS6
<b>UPC</b>	<b>Product Length/Depth</b>
781011403348	1.75 in
<b>Product Height</b>	<b>Product Width</b>
0.85 in	1.31 in
<b>Product Weight</b>	<b>Certifications</b>
0.07 lb	Not Applicable

## Model

### Bolt/thread/rod size

1/4"-20

### Product Category

Channel nuts

### Type

Nut with spring

## Load rating/capacity

### Load rating (pull out strength)

250 lbs

### Load rating (slip strength)

300 lbs

## Material/finish

### Finish

Stainless steel type 316

### Material

Steel

## Resources

### Catalogs

[B-Line Series Strut Systems Catalog](#)

[B-Line Safety Gratings Full Catalog](#)

[Channel Nuts and Hardware Catalog Section](#)

### Specifications and datasheets

[Eaton Specification Sheet - N224SS6](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)