



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



N250SP 250 Al/Cu Split Bolt

Nsi Industries

Catalog Number	N250SP
Manufacturer	Nsi Industries
Description	
Weight per unit	0.5700 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	TIN PLATED COPPER
Number of Conductors	2 IN
Poles	1 IN
Voltage Rating	600 VAC
Wire Size	1/0 STR - 250 MCM
Wire Type	Class A & B

Material, Color, and Finish

Color	SILVER
Finish	Tin Plated Copper

Dimensions and Weight

Size	L=2.106 - W=1.102 IN
------	----------------------

Descriptions

Description	250 AL/CU SPLIT BOLT
Product Type	Copper Split Bolt 250 Tin Plated
Special Features	1/0 SOL-250 MCM - 6 Pack

Manufacturer Information

Brand	NSi
GTIN	00662381020390
Manufacturers Part Number	N-250SP
sub brand	Split Bolts
UPC	662381020390

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Tin Plated Copper Split Bolt

Packaging

Carton	1
Package	6
Weight Per each	0.57



ELLIOTT ELECTRIC SUPPLY


We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 WTT
standard	UL486B
Temperature Rating	90 WTT

All Purpose Type Split Bolts - N-250SP



Drawn - SD

Approved - KM

Material - Copper / Finish: Tin Plated

Title - All Purpose Type Split Bolts



Max Run To Max Tap	250 - 250 STR AL-CU
Min Run To Min Tap	4/0 - 8 STR AL-CU
Max Run To Min Tap	250 - 8 STR AL-CU
Min Equal Run - Tap	1 - 1 STR AL-CU
4	Spacer Electrolytical Copper
3	Nut Bronze
2	Rider Bronze
1	Body Electrolytical Copper

