


All Purpose Type Split Bolts - N-350SP



Drawn - SD

Approved - KM

Material - Copper / Finish: Tin Plated

Title - All Purpose Type Split Bolts



Max Run To Max Tap	350 - 350 STR AL-CU
Min Run To Min Tap	350 - 1/0 STR AL-CU
Max Run To Min Tap	350 - 1/0 STR AL-CU
Min Equal Run - Tap	2/0 - 2/0 STR AL-CU
4	Spacer Electrolytical Copper
3	Nut Bronze
2	Rider Bronze
1	Body Electrolytical Copper

