ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

N6 #6 Cu Split Bolt

Nsi Industries

Catalog Number	N6
Manufacturer	Nsi Industries
Description	Split Bolt Connector, #10 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, #6 Awg (Range Of Equal Main and Tap-Stranded);#16 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper;Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 0.866 In Overall Length, Split Terminal, 600 V, 0.055 LB/Ea
Weight per unit	0.0550 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	10 SOL - 6 SOL
Wire Type	Class A & B

Material, Color, and Finish

Color	Copper
Finish	COPPER
Housing Material	Copper

Dimensions and Weight

Size	L=.866 - W=.492

Descriptions

Description	#6 CU SPLIT BOLT
extra long description	NSI N-6 Split Bolt Copper 6
Features	Copper Split Bolt Connector 6 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.

Manufacturer Information

GTIN	00662381020024
UPC	662381020024

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Copper Split Bolts

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.055

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B