


All Purpose Type Split Bolts - N-6SP

Drawn - SD		
Approved - KM		
Material - Copper / Finish: Tin Plated		
Title - All Purpose Type Split Bolts		
		
Max Run To Max Tap	6 SOL AL CU	
Min Run To Min Tap	8 - 14 STR AL CU	
Max Run To Min Tap	6 SOL - 14 STR AL CU	
Min Equal Run - Tap	8 - 8 STR AL CU	
4	Spacer	Electrolytical Copper
3	Nut	Bronze
2	Rider	Bronze
1	Body	Electrolytical Copper

