



**SKU:** N-87

**UPC:** 0783669015485

**Features & Benefits:**

**Description:** Copper Ground Bar, Conductor Range 6-14, 87 ports, UL

## Specs

### Additional Class Attributes

Connection	Mechanical
Mounting Hole Type	NA
Number of Conductors	87
Number of Poles	1
Type of Accessory	E-153

### Material and Finish

Conductor Material	Copper
Connector Finish	NA
Insulation	NA
Material	Copper

### Dimensions

Drive Size Main	NA
Drive Type Main	NA

### Additional Technical Specifications

Conductor Type	Solid
----------------	-------

### Bolt and Screw Sizes

Mounting Bolt/Stud Size	NA
Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	NA

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 1
Dual Rated	No
NEMA Code	S-588-3
UPC Code	78366901548

## Conductor Ranges

Conductor Range CU Solid (Primary, run, main, line)	10 Sol - 14 Sol
Conductor Range CU Stranded (Primary, run, main, line)	6 Str - 14 Str

## Testing Standards

Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL / CULUS Specification	UL 467 Listed
UL File Number	E6207

## Color

Color	Copper
-------	--------