



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NFFLDC40S SLPFTR 128W Led Flood 40K

*Cooper Lighting Solutions*

Catalog Number	NFFLDC40S
Manufacturer	Cooper Lighting Solutions
Description	Led Flood Light, Die-Cast Aluminum, 120 to 277 V Ac;347 V Ac;480 V Ac, 128 W, 70, 16900 LM Brightness (Lumens), 4000 K, Powder Coat, 15-15/16 In Length, 8-11/16 In Width, 12-11/16 In Height, Tempered Glass Lens Material, Slipfitter Mount, +40 °C Operating Temperature, -40 °C Operating Temperature, 60000 H Average Life, 5 Yr Warranty, 20 LB
Weight per unit	19.7 (lbs/each)
Product Category	Led Floodlights

### Features

amperage rating	0.466 (at 277V)
Ballast Type	N/A
battery	N/A
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	16,932
Number of Lamps	2
Shape	Rectangular

### Dimensions and Weight

Size	23.0 IN Length 19.0 IN Width 10.0 IN Height
------	---

### Descriptions

Description	SLPFTR 128W LED FLOOD 40K
extra long description	CLS NFFLD-C40-S NFFLD,129W,4000K,UN
Special Features	Die-cast aluminum housing, driver compartment and driver door

### Manufacturer Information

Brand	LUMARK
GTIN	00080083801206
UPC	080083801206

### Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

### Packaging

Carton	1
Weight Per each	19.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Mounting  
standard

SLIPFITTER

UL/cUL Listed - Wet Location;RoHS Compliant