



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NFFLDLC100S 252W Led LRG Flood 40K 33900LM

Cooper Lighting Solutions

Catalog Number	NFFLDLC100S
Manufacturer	Cooper Lighting Solutions
Description	Led Flood Light, Construction and Storage Sites;Light Industrial Locations;Marinas and Service Areas;Parking Lots;Rail Yards, 33941 LM Brightness (Lumens), Black, 70 Color Rendering Index, 4000 K Color Temperature, 0.923 A @ 277 V;2.141 A @ 120 V Current Rating, Powder Coated Finish, 27-1/2 In;699 MM Height, IP66 Ip Rating, Led Lamp Type, 16 In;406 MM Length, Glass Lens Material, Die Cast Aluminum Material, +40 °C Maximum Operating Temperature, -40 °C Minimum Operating Temperature, Slip Fitter Mount, 4 - L
Weight per unit	47.8 (lbs/each)
Product Category	Led Floodlights

Features

amperage rating	0.91 (at 277V)
Ballast Type	N/A
battery	N/A
Fixture Type	FLOODLIGHT
lumens	33941
Shape	Rectangular

Dimensions and Weight

Size	31.0 IN Length 18.25 IN Width 11.0 IN Height
------	--

Descriptions

Description	252W LED LRG FLOOD 40K 33900LM
extra long description	CLS NFFLD-L-C100-S NFFLD-L C100 UNV
Special Features	Die-cast aluminum housing, driver compartment and driver door

Manufacturer Information

Brand	LUMARK
GTIN	00080083800889
Manufacturers Part Number	NFFLD-L-C100-S
UPC	080083800889

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	47.75

Uses, Certifications, and Standards

Mounting	SLIPFITTER
standard	UL/cUL Listed - Wet Location;RoHS Compliant