



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NK6PC7BUY NK Copper Patch Cord Cat 6 Blue Utp Cable 7 FT

Panduit Corporation

Catalog Number	NK6PC7BUY
Manufacturer	Panduit Corporation
Description	The Netkey® Cat 6 Utp Patch Cord Is Constructed Of 24 Awg, Unshielded, Twisted Pair, Stranded, CM Cable With Enhanced Performance Modular Plugs. The Patented Tangle Free Latch Prevents Snags and Provides Easy Release Saving Time On Frequent Moves, Adds, and Changes. The Patch Cord'S Slender Strain Relief Boot Provides Easy Access In High-Density Applications. The Patch Cord Is 7 Feet In Length and Blue.
Weight per unit	0.2100 (lbs/each)
Product Category	Wire

Features

media	Yes
outside diameter	0.235
Plug Type	Modular Plug
Wire Size	24

Material, Color, and Finish

Color	Blue
Jacket Material	Polyvinyl Chloride (PVC)

Dimensions and Weight

Length	7.00
--------	------

Descriptions

Description	NK COPPER PATCH CORD CAT 6 BLUE UTP CABLE 7 FT
extra long description	PAN NK6PC7BUY NetKey® Cat 6 24 AWG
Long Description	The NetKey® Cat 6 UTP Patch Cord is constructed of 24 AWG, unshielded, twisted pair, stranded, CM cable with enhanced performance modular plugs. The patented tangle free latch prevents snags and provides easy release saving time on frequent moves, adds, and changes. The patch cord's slender strain relief boot provides easy access in high-density applications. The patch cord is 7 feet in length and blue.
Product Type	Netkey® Cat 6 24 Awg Utp Patch Cord, 7 FT, Blue

Manufacturer Information

Brand	PANDUIT
GTIN	00074983055708
Manufacturers Part Number	NK6PC7BUY
UPC	074983055708



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type	Patch Cord
------	------------

Packaging

Carton	1
Package	10
Weight Per each	0.21

Uses, Certifications, and Standards

Application	155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM;Token;Used in all work area outlets and patch panels;wired to be compatible with both T568A and T568B wiring schemes. Suitable for Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), and 1000BASE-T (Gigabit Ethernet)
standard	Complies with ANSI/TIA-1096-A;Exceeds ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E channel requirements at swept frequencies up to 250 MHz;Meets ANSI/TIA-568.2-D and ISO 11801 Category 6 component requirements at swept frequencies up to 250 MHz