#### White Button® Non-Metallic Cable Connectors

# more on

## Easy, Push-in Installation from Inside or Outside the Box



Save money with Arlington's non-metallic NM cable connectors. They're the *lowest* cost NM cable connectors on the market, and the fastest to install! Simply push the connector into the knockout, and you're done.

Listed for single or multiple cables,
Arlington's new White Button® connectors
offer smooth, easy cable insertion of
one or two cables into a single opening
from the INSIDE or OUTSIDE the box.

#### Better than our popular NM94 and NM95 – at the same cost!

Cable Ranges

1/2" NM94X	3/4" NM95X
One 14/2 to 6/2	One 14/2 to 6/2
One 14/2/2	One 14/3 to 6/3
One 12/4	One 12/4
One 12/2/2	One 12/2/2
One 14/3 to 10/3	
Two 14/2 to 10/2	Two 14/2 to 10/2
Two 14/3	Two 14/3 to 10/3
Two 12/3	
One 14/2 & One 12/2	One 14/2 & One 12/2
One 14/2 & One 10/2	One 14/2 & One 10/2
One 12/2 & One 10/2	One 12/2 & One 10/2
	One 14/3 & One 12/3
	One 14/2 NMB-PCS
	One 12/2 NMB-PCS
200	One 14/2 to 10/2 NMD90
NM95X on NMD90	Two 14/2 to 10/2 NMD90

- NM95X works with the new NMB-PCS cable – and Canada's NMD90 cables
- Easy removal with pliers or screwdriver
- UL Listed exceeds UL and CSA pullout requirements







#### **Arlington®**

1 Stauffer Industrial Park Scranton, PA 18517

800/233.4717 • Fax 570/562.0646 www.aifittings.com

## Lowest Cost NM Cable Connector • Easy, Push-in Installation

- · Listed for one or two cables
- · Easy installation
- · Smooth, easy cable insertion
- Secure hold on cable exceeds UL pullout tests

In	a	connector with	TWO SEPARATE
op	e	nings: NM942	( ) A



CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997 wi	DESCRIPTION/SIZE NM Cable Connectors th TWO individual openings	COLOR/ KO SIZE	CABLE RANGES	UNIT PKG	STD PKG
NM942 Black Button®	04281	3/8" Trade Size	Black 1/2"	One or Two 14/2 One or Two 12/2 One 14/2 and One 12/2 One or Two 10/2	250	1000



1 from OUTSIDE new work box Push NM942 into KO with light finger pressure.



2 Insert one or two cables into individual openings.



3 To remove from KO. Slip screwdriver under connector and twist.

#### In a connector with a SINGLE opening

insert TWO cables together or individually into NM94, NM95 or NM96. Add a second cable without removing the first.



1 from OUTSIDE box push the NM cable connector into KO with light finger pressure.



2 Insert one or two cables in a single opening, fast! Push the NM cable(s) into the connector to the desired length.

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION/SIZE NM Cable Connector with SINGLE opening	KO SIZE	CABLE RANGES	UNIT PKG	STD PKG
NM94 NM940	05488 72156	3/8" Trade Size 3/8" Trade Size Black Button®	1/2" 1/2"	One 14/2 to 6/2 One 12/4 One 12/4 One 14/3 to 10/3 Two 14/2 to 10/2 Two 14/3 Two 12/3 One 14/2 and One 12/2 One 14/2 and One 10/2 One 12/2 and One 10/2 One 14/3 and One 12/3	250 100	1000
NM95	10956	3/4" Trade Size Black Button®		One 14/2 to 6/2 One 14/3 to 6/3 One 14/2/2 One 12/4 Two 14/2 to Two 10/2 Two 14/3 to Two 10/3 One 14/2 and One 12/2 One 14/2 and One 10/2 One 14/3 and One 12/3 One 14/3 and One 12/3 One 14/2 NMB-PCS One 12/2 NMB-PCS One 14/2 to 10/2 NMD90 Two 14/2 to 10/2 NMD90	50	500
NM96	72158	1" Trade Size Black Button®	1"	One 4/3 to 8/3 One 6/2 to 4/2	25	250



c (ÎL)

### **Arlington**®

1 Stauffer Industrial Park Scranton, PA 18517 800/233.4717 • Fax 570/562.0646 www.aifittings.com



Distributed by