

Cable Stacking Support - Nonmetallic

Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 4.750
Dimension B in Inches: 1.938
Dimension C in Inches: .750
Dimension D in Inches: .500

Application

The NMCB-3 is provided with nails for use on wood studs or 3/4" thick furring strips to position non-metallic sheath cable. Capable of positioning up to five 14/2 to 10/3 AC or MC cables or two 14/2 NM cables in each of three rectangular slots. May also be used to be attached to metal studs or enclosures, or concrete block with #6 round head screws. Mounts in either horizontal or vertical direction. Low voltage design and unique dimpled slots prevent accidental removal of cables.

Product Information

Material: Polypropylene

Certifications & Codes:

UL File Number: E161206
UL Standard: UL2239
UNSPSC: 39121705

Catalog ID: NMCB-3

UPC Number: 78174740767

Description: NM Cable Support Stacker

Application: The NMCB-3 is provided with nails for use on wood studs or 3/4" thick furring strips to position non-metallic sheath cable. Capable of positioning up to five 14/2 to 10/3 AC or MC cables or two 14/2 NM cables in each of three rectangular slots. May also be used to be attached to metal studs or enclosures, or concrete block with #6 round head screws. Mounts in either horizontal or vertical direction. Low voltage design and unique dimpled slots prevent accidental removal of cables.

Std Pkg Qty: 100

Unit Qty: 25