



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NMLT50 1/2" Sealtight Straight Nonmetallic Connector

*Arlington Industries*

Catalog Number	NMLT50
Manufacturer	Arlington Industries
Description	Non-Metallic Straight Connector, 1/2 In Trade Size, Plastic, Gray, 1.425 In Length, 1.421 In Diameter, Threaded X Screw-In Connection, 1/2 In Knockout Size, 0.038 LB/Ea
Weight per unit	0.0400 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

connection	Threaded X Screw-In
Form	Form B
Material	UV-Rated Plasti

### Material, Color, and Finish

Color	Gray 0
-------	--------

### Dimensions and Weight

Size	L(1.545) x W(1.410) x H(1.410) IN
------	-----------------------------------

### Descriptions

Description	1/2" SEALTIGHT STRAIGHT NONMETALLIC CONNECTOR
-------------	---

### Manufacturer Information

GTIN	00018997545008
UPC	018997545008

### Taxonomies, Classifications, and Categories

Category Description	NON-METALLIC FITTINGS
Type	Straight Connector

### Packaging

Carton	25
Package	100
Weight Per each	0.04

### Uses, Certifications, and Standards

standard	UL and CSA
----------	------------



# Arlington

## Part : NMLT50

Description: Straight Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.038 lbs/each

Height: 1.421"

Width: 1.425"

Additional Color Options:  height="16" width="16"/>

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 1/2"

## Packaging

Unit: 25 pcs

Standard: 100 pcs

