

NRG® 1100

Compact Wallpack – Full Cut-off

Hubbell Outdoor Lighting's NRG® 1100 family is packed with owner benefits. The IDA compliant optics allow no up light, saving energy and keeping the neighbors happy!

Two sets of recessed closure screws are included – Phillips head and tamper resistant allen head.

For wall perimeter or entry at mounting heights of 8-15 feet. Decorative rugged styling with one piece polycarbonate front, painted bronze or white on the inside, that resists rocks and other small projectiles. The die-cast housing provides rigid mounting, conduit and photocontrol hubs, easy mount design and heat dissipation.

Listed to UL1598 for use in wet locations



HID WALLPACKS

STOCK ORDERING INFORMATION

Catalog Number ¹	Wattage/Voltage	Finish	Weight lbs. (kg)	PKG. CODE
NRG-1111-W	100w PSMH, 120, 277, 347V	white	12 (5.4)	FCC
NRG-1112-W	100w HPS, 120, 277, 347V	white	10 (4.5)	BC
NRG-1151-W	50w, 120, 277	white	9 (4.1)	BC
NRG-1172-W	70w HPS, 120, 277, 347V	white	9 (4.1)	BC
NRG-1143-W	42w CFL, 120-277V, 60/50hz	white	7 (3)	FCC

¹ All fixtures include medium base or compact fluorescent lamps. CFL units use universal socket and are capable of operating 26 or 32w PLT lamps if substituted in the field; CFL lamps are 3500K, GX24q-4 base


STOCK ACCESSORIES - Order Separately

Catalog Number	Description	PKG. CODE
PBT-1	Photocontrol, button type, 120V	SCC
PBT-234	Photocontrol, button type, 277V	SCC

MADE-TO-ORDER REPLACEMENT PARTS

Catalog Number	Description	PKG. CODE
NRG1100FHB	Polycarbonate front housing-bronze, 70w max.	BC
NRG1100FHW	Polycarbonate front housing-white, 70w max.	BC
NRG1111FHB	Polycarbonate front housing-bronze, 100w max.	BC
NRG1111FHW	Polycarbonate front housing-white, 100w max.	BC

DIMENSIONS



A	B	C
11 3/4"	9 1/2"	9 1/2"
298 mm	241 mm	241 mm



HUBBELL
Outdoor Lighting