

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

NRG 300 SERIES

PERIMETER WALL PACK

FEATURES

- New higher output plus increased lumens per watt
- 4000K and 5000K high 80 CRI LEDs provide optimal color recognition
- 1,800+ lumens at 110+ LPW
- Universal voltage 120-277V (including photocontrol)
- Non-cutoff retractor fills surrounding area with safety/security illumination
- ½ bottom knockout for surface conduit wiring
- Rigid cast aluminum back housing
- One-piece polycarbonate front
- Tamper proof hardware included



SPECIFICATIONS

CONSTRUCTION

- Full polycarbonate front provides vandal resistance and efficient spread of forward and lateral light coverage
- Internally painted bronze finish for lasting appearance
- LED unit is an excellent upgrade from HID systems featuring a 17w LED system with a 1700+ lumen output, 4000K or 5000K CCT, 80 CRI - 60,500 hr rated life at L94
- Rugged cast aluminum back housing for rigid mounting; Bottom 1/2" conduit knockout for surface conduit wiring. Back hub allows access to recessed wiring boxes; Two point mounting; Additional center-pin torx screws provided for tamper-resistant applications

OPTICS

- Single driver 50/60 Hz, 120-277V
- NRG-356L is 1858/1794 lumens, 4000K/5000K, 112/110 IPW, CRI 80
- PC version 120V-277V

CERTIFICATIONS

- Listed to UL 1598 for use in wet locations

WARRANTY

- 5 Year warranty

tradeSELECT®



KEY DATA	
Lumen Range	1794–1858
Wattage	16.6
Efficacy Range (LPW)	110–112
Fixture Projected Life (Hours)	L70 > 50K
Weight lbs. (kg)	6 lbs. (2.7kg)

NRG 300 SERIES

PERIMETER WALL PACK

ORDERING INFORMATION

Catalog Number	Without Photocontrol	Wattage	Voltage	Max Input Amps	Color	Weight lbs. (kg)
	NRG-356L-4K-U	16.6W	120-277V	.15	Dark Bronze Matte Textured	6 (2.7)
	NRG-356L-5K-U	16.3W	120-277V	.15	Dark Bronze Matte Textured	6 (2.7)

ACCESSORIES

Catalog Number	Description
PBT-1	Button photocontrol, 120V
PBT-234	Button photocontrol, 208, 240, 277V

DIMENSIONS

