



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

106 Industrial Drive
71292-0000, LA West Monroe
Phone: 318-398-9757
Fax: 318-398-9704



NT054FB3 54" FB Nitro Outdoor Fan

Craftmade International I

Catalog Number	NT054FB3
Manufacturer	Craftmade International I
Description	Indoor or Outdoors, The Wet-Rated Nitro 54" By Craftmade Features Custom Abs Blades, An Optional 22W Dimmable Led Light With An Optional Lens Cover, and A Standard, 3-Speed Reversible Motor With Wall and Remote Controls to Deliver Airflow Performance Wrapped In Sleek Modern Style.
Weight per unit	16.2 (lbs/each)
Product Category	20240402120417

Features

bulb type	LED
Category	Fans
Safety Rating	Wet
Voltage	120.00

Material, Color, and Finish

Finish	Black
Style	Contemporary Modern

Descriptions

Description	54" FB NITRO OUTDOOR FAN
Long Description	Indoor or Outdoors, the wet-rated Nitro 54" by Craftmade features custom ABS blades, an optional 22W dimmable LED Light with an optional lens cover, and a standard, 3-speed reversible motor with wall and remote controls to deliver airflow performance wrapped in sleek modern style.
Product Type	54"Ceiling Fan

Manufacturer Information

Brand	CRAFTMADE
GTIN	00647881250805
Manufacturers Part Number	NT054FB3
UPC	647881250805

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Wet Location

Packaging

Carton	1
Weight Per each	16.2