



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7929 N Sam Houston Pkwy W Suite 100
77064-0000, TX Houston
Phone: 281-345-1143
Fax: 281-345-7697



NTCC150 1-1/2" Rigid Threadless Raintight Coupling

Appleton/Oz Gedney

Catalog Number	NTCC150
Manufacturer	Appleton/Oz Gedney
Description	Coupling, Trade Size: 1-1/2 In, Outside Diameter: 2.69 In, Length: 3.31 In, Flexibility: Rigid and Imc, Material: Malleable Iron, Connection: Compression, Standard: UI 514B, UI File Number E11853, Nema FB-1, For Joining Lengths Of Steel Emt to Rigid Metal Conduit or Imc
Weight per unit	1.2 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Compression
outside diameter	2.69

Dimensions and Weight

Length	3.31
--------	------

Descriptions

Description	1-1/2" RIGID THREADLESS RAIN TIGHT COUPLING
extra long description	APP NTCC-150 1-1/2 IN CPLG NO THRD
Long Description	Coupling, Trade Size: 1-1/2 IN, Outside Diameter: 2.69 IN, Length: 3.31 IN, Flexibility: Rigid And IMC, Material: Malleable Iron, Connection: Compression, Standard: UL 514B, UL File Number E11853, NEMA FB-1, For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
Product Type	1-1/2 In CPLG No THRD RGD Cond
Special Features	Threadless, Concretetight

Manufacturer Information

Brand	Appleton
GTIN	00781381638401
Manufacturers Part Number	NTCC-150
UPC	781381638401

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	COUPLING

Trade Size

Trade Size	1-1/2
------------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7929 N Sam Houston Pkwy W Suite 100
77064-0000, TX Houston
Phone: 281-345-1143
Fax: 281-345-7697

Packaging

Carton	5
Package	25
Weight Per each	1.18

Uses, Certifications, and Standards

Application	For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
standard	UL 514B, UL File Number E11853, NEMA FB-1