

## Incandescent

# 6" Remodel Housing IC & Non-IC

#### Recessed

Туре	
P187-TG	

		Dimensions (Inches)			
Catalog No.	Lamping	Α	В	C	D
P187-TG	See Trim Specifications		7-1/2 Openir	7-1/8 ng 6-5/8	15-1/2
	B A A				

## **Specifications:**

#### Wiring

- 1/2" Knock outs
- Grounding pigtail

#### Construction

- Housing adjusts from 1/2 " to 1-1/2 " thick ceilings
- Galvanized steel construction
- Porcelain socket with nickel-plated brass screw shell
- Socket can be used as work light
- Adjustable slide bars lock unit securely to ceiling

#### Labeling

- IC & Non-IC listed
- UL-CUL listed for damp location and feed-through wiring (2in, 2out, 12ga.)
- Approved for use in new York city per calendar #40330

### Lamp/Trim

- Trim mounted socket for optimum performance
- Trim-Lok® action forces trim to fit snugly against the ceiling

Note: When used with P8593-01 gasket kit, P187-TG is certified to meet ASTM E283 air tight requirements when installed properly per instructions.