

P2610 Fan Light Kit

Description:

Four-light kit with white washed alabaster style glass shades beautiful in design. Innovative spring clip glass attachment system eliminates unsightly excess hardware. Good for use with P2500 and P2501 ceiling fans and includes quick connector for easy wiring. Includes four 3000K, 800 lumen, Title 24 certified LED bulbs.

Specifications:

- Brushed Nickel (-09) (Plated)
- Steel constructionAlabaster glass ConeAlabaster style white washed glass shades
- Brushed Nickel finish
- Good for use with Progress Lighting ceiling fans: P2500, P2501, P2524 and P2525 ceiling fans and P2502 indoors.
- · Innovative spring clip glass attachment system- eliminates hardware.
- Includes four 3000K, 800 lumen, Title 24 certified LED bulbs
- Fan quick connect wiring.
- Energy Star Qualified
- Meets California T24 JA8-2016
- · Mounting No for outlet box included
- 6" of wire supplied
- ·

Performance:

Number of Modules	4	Di
Input Power	10w	D
Input Voltage	120 V	Н
Input Frequency	60 Hz	G
Lumens/LPW	800/80 (LM-79)	Ŵ
ССТ	3000 K	He
CRI	90 CRI	
Life (hours)	25,000 (L70/TM-21)	
EMI/RFI	Title 24	
Min. Start Temp	-10 °C	
Max. Operating Temp	40 °C	
Warranty	1 year warranty	
Labels	UL Dry location listed	

Project:

Fixture Type: Location:

Contact:

Dry location listed PROGRESS LED

P2610-09WB

Images:



Dimensions:

Diameter: 15" Height: 6-1/4"

Glass Width: 5-3/8" Height: 4-7/8"