

roject:	
ixture Type:	
ocation:	
ontact:	

P2610 Fan Light Kit

• Dry location listed PROGRESS LED

Description:

Four-light kit with white washed alabaster style glass shades beautiful in design. Innovative spring clip glass attachment system eliminates unsightly excess hardware. Good for use with P2500 and P2501 ceiling fans and includes quick connector for easy wiring. Includes four 3000K, 800 lumen, Title 24 certified LED bulbs.

Specifications:

- · Antique Bronze (-20) (Painted)
- Steel constructionAlabaster glass ConeAlabaster style white washed glass shades
- · Antique Bronze finish.
- Good for use with Progress Lighting ceiling fans: P2500, P2501, P2524 and P2525 ceiling fans and P2502 indoors.
- · Innovative spring clip glass attachment system- eliminates hardware.
- Includes four 3000K, 800 lumen, Title 24 certified LED bulbs
- Fan quick connect wiring.
- Energy Star Qualified
- · Meets California T24 JA8-2016
- · Mounting No for outlet box included
- 6" of wire supplied

Performance:

Number of Modules	4
Input Power	10w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	800/80 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	25,000 (L70/TM-21)
EMI/RFI	Title 24
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	1 year warranty
Labels	UL Dry location listed

P2610-20WB

Images:



Dimensions:

Diameter: 15" Height: 6-1/4"

Glass

Width: 5-3/8" Height: 4-7/8"