

DATE: TYPE:

NAME:

PROJECT:

Incandescent



Ashmore

Two-light Indoor/Outdoor fan light kit with univesal style. Classic old world styling, the Ashmore Collection features a seeded water glass diffuser to reduce glare and to minimize cleaning requirements. Antique Bronze finish correpsonds with an Antique Brass pull chain and walnut fob. Quick connect wiring available with fans that accept an accessory light.

Category: Ceiling Fans Finish: Antique Bronze (powdercoat) Construction: Steel construction construction Glass: Frosted seeded glass bowl

Diameter: 11-1/16" Height: 8-1/4"

Glass: 10-1/8" dia. Height: 3-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling fan light kit mounted	Pre-wired Quick-connect wiring 6" of wire supplied 120V	Quantity: 2 60W Medium Base (included) Medium sockets 13w CFL non-dimmable (included)	UL-CUL Damp location listed 1 year warranty Antique brass pull chain with walnut fob Companion Ceiling Fans,Chain hung lantern, Close-to-ceiling, Landscape, Post top lantern, Wall lantern fixtures are available