

Eaton P2LM2CA2/UNV1

Catalog Number: P2LM2CA2/UNV1

Eaton Crouse-Hinds series Vaporgard Pro P2L LED, 0.12A, Cool white, AC drive, 50W HID or 150-200W incan equiv, 50/60 Hz, Without guard, Heat and impact resistant glass lens, 1700 lm, Copper-free alum, Pend mt, 3/4", 120-277 Vac, 14W



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Vaporgard Pro P2L LED light fixture	P2LM2CA2/UNV1
	UPC
	662276840140
Product Length/Depth	Product Height
8.75 in	4.69 in
Product Width	Product Weight
8.75 in	5.7 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lumens

1700

Color temperature

Cool white

Mounting Method

Pendant

Trade size

3/4"

Voltage rating

120-277 Vac

Drive type

AC

Frequency rating

50/60 Hz

Lens material

Heat and impact resistant glass

Wattage

14W

Amperage Rating

0.12 A

Material

Copper-free aluminum

Power factor

> 0.9

Guard

Without guard

Equivalent luminaire

50W HID or 150-200W incandescent

Resources

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Vaporgard Pro P2L/P3L LED brochure](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

Catalogs

[Crouse-Hinds series Vaporgard Pro P2L/P3L LED catalog page](#)

Certification reports

[Vaporgard Pro P2L Industrial LED Light Fixtures Canadian certification](#)

Installation instructions

[IF 1627 - Vaporgard Pro P2L LED](#)

[IF 1884 - Vaporgard Pro Driver Modules - AC Version](#)

Specifications and datasheets

[Eaton Specification Sheet - P2LM2CA2/UNV1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)