

Project:
----------

Fixture Type: Location:

Contact:

Everlume

# Wall or Ceiling Mounted • Damp Location Listed PROGRESS LED

### **Description:**

Everlume Collection 1-Light Satin White Frosted Glass LED Modern Bath Vanity Linear Panel Light

# **Specifications:**

- Frosted Polystyrene Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Frame covers a standard 4" recessed outlet box: 13.78 in W., 0.78 in ht., 4.37 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

#### **Performance:**

Number of Modules	1
Input Power	26 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,253/86 (LM-79)
ССТ	3000 K
	4000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2019





## **Dimensions:**

Length: 24.02 in Extends: 1.38 in Height: 5 in H/CTR: 2-1/2 in

Frosted Polystyrene Diffuser Width: 0.39 in Height: 4 in



# Everlume

Wall or Ceiling Mounted • Damp Location Listed PROGRESS LED

P300305-028-CS

#### **Dimming Notes:**

 $\mathsf{P300305}\text{-}\mathsf{028}\text{-}\mathsf{CS}$  is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls:**

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.