

Project:			
Fixture Type:			
Location:			
Contact:			

## **P3474-20** Trinity

Three-light hall and foyer fixture featuring soft angles, curving lines and etched glass shades. Gracefully exotic, the Trinity Collection offers classic sophistication for transitional interiors. Sculptural forms of metal and glass are enhanced by a classic finish. This transitional style can transform a room or your whole home with its charming versatility. Antique Bronze finish.

- · Antique Bronze finish.
- · Etched glass shades with slight banding.
- · Sophisticated style for interior design.
- · Graceful, soft angles with curving lines.

Category: Hall & Foyer

**Finish:** Antique Bronze (Painted) **Construction:** Steel Construction

Glass/Shade: Etched glass inverted bowl style



Diameter: 18 in Height: 24 in

Overall Ht. W/Chain: 99 in

Etched glass inverted bowl style

Width: 16 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Three 100 W max. Medium Base	UL-CUL Dry Location Listed
Mounting strap for outlet box included	15 feet of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E26 base ceramic sockets	
Canopy covers a standard 4" recessed outlet box: 5.5" W., 1.375" ht., 5.5" depth			